


PEROXAN DC-Paste 50 SI/3

Dialkyl peroxide / Crosslinking

Description

Dicumyl peroxide
50%, Paste in silicone oil

PEROXAN DC-Paste 50 SI/3 is used for the crosslinking of silicone rubber.



Molecular weight:

270.4

CAS No.:

80-43-3

Technical data

Appearance:

white paste

Peroxide assay:

appx. 50%

Active oxygen assay:

appx. 2.96%

Density at 20°C:

1.05 g/cm³

Half life time

in an EPDM compound:

t _{1/2}	10h	1h	0,1h
bei	112°C	138°C	162°C

Storage

Maximum storage temperature (Ts max):

30°C

Minimum storage temperature (Ts min):

5°C

Storage stability as from date of delivery:

6 months

Hazardous reactions

Organic Peroxides are more or less stable products but will decompose under the influence of heat. To minimize a loss of quality during storage, it is important that the recommended maximum storage temperature is not exceeded. If a minimum storage temperature is given, an undesirable process such as a solidification or phase separation, is known to occur below this temperature.

Safety characteristics

SADT:

80°C

The SADT (Self Accelerating Decomposition Temperature) is the lowest temperature at which a self accelerating decomposition may occur.

PEROXAN DC-Paste 50 SI/3

Dialkyl peroxide / Crosslinking

Application

PEROXAN DC-Paste 50 SI/3 is recommended for the crosslinking of silicone rubber. Rubber compounds containing PEROXAN DC-Paste 50 SI/3 combine good processing safety with a fair speed of cure.

Safe processing temperature (t₂): 130°C

Typical crosslinking temperature (t₉₀): 170°C

The safe processing temperature t₂ is defined as the temperature, at which the scorch time is longer than 20 minutes. The typical crosslinking temperature t₉₀ is defined as the temperature at which 90% of the crosslinks in the compound are formed within about 12 minutes.

Packaging

20kg pail

Major decomposition products

2-Phenylpropanol-2, acetophenone, alpha-methylstyrene, Methane

Safety and handling

Please refer to the material safety data sheet (MSDS) for information concerning safe storage, use and handling of PEROXAN DC-Paste 50 SI/3. This information should be thoroughly reviewed prior to acceptance of this product. The MSDS is available for downloading at www.pergan.com or through contacting Pergan directly.

The information presented herein is true and accurate and to the best of our knowledge, but without any guarantee. Since the conditions of use are beyond our control we disclaim any liability, including for patent infringement, incurred in connection with the use of these products, data or suggestions.